

## UP-168, platform

## DESCRIPTION

Universal platform with clamps can accommodate flasks or bottles of different volume sizes. Clamps are not included with platform and need to be ordered separately.



## CAT. NUMBER

BS-010135-JK

Platform UP-168

## ACCESSORIES



**TR-44/15**BS-010135-LK rack

Adjustable angle test tube rack for UP-168



**TR-21/50**BS-010135-KK rack

Adjustable angle test tube rack for UP-168



**FC-50** BS-010126-MK clamp

Clamp 50 ml - Ø50 mm for UP-168



FC-100 BS-010126-HK clamp

Clamp 100 ml - Ø65 mm for UP-168



FC-250 BS-010126-JK clamp

Clamp 250 ml - Ø85 mm for UP-168



FC-500 BS-010126-LK clamp

Clamp 500 ml - Ø105 mm for UP-168



FC-1000 BS-010126-IK clamp

Clamp 1000 ml - Ø130 mm for UP-168



FC-2000 BS-010126-NK clamp

Clamp 2000 ml - Ø165 mm for UP-168



HSC-50 BS-010167-DK clamp

Tight fit clamp 50 ml - Ø50 mm for UP-168



**HSC-100** BS-010167-EK clam

Tight fit clamp 100 ml - Ø65 mm for UP-168

UP-168, platform Page 1 of 2



**HSC-250** BS-010167-FK clamp

Tight fit clamp 250 ml - Ø85 mm for UP-168



**HSC-500** BS-010167-JK clamp

Tight fit clamp 500 ml -Ø105 mm for UP-168



**HSC-1000** BS-010167-IK clamp

Tight fit clamp 1000 ml - Ø130 mm for UP-168



ES-20/60 Without platform Orbital Shaker-Incubator

Orbital Shaker–Incubator ES-20/60 for biotechnological and pharmaceutical laboratories is a professional category equipment designed for cultivation of microorganisms and eukaryotic cells including animal, plant and insect cells. It is also ...

read more



ES-20/80 Without platform Orbital Shaker-Incubator

ES-20/80 shaker-incubator for biotechnological and pharmaceutical laboratories is a professional category equipment. The typical applications include - microbial and cell culture cultivation, protein expression, solubility studies, general mixing, as well

read more



PSU-20i Without platform Multi–functional Orbital Shaker

Shaker PSU-20i provides three motion types: orbital, reciprocal and vibrating, which can be performed separately, pairwise and sequentially in repeated cycles. Shaker is designed for applications both in small specialized ...

read more

UP-168, platform Page 2 of 2